



Vibration measurement

XT280



EASY TO USE

Easy-Laser® XT280 is an easy-to-use vibration monitoring and analysis tool that allows easy display of vibration signals. The XT280 automatically performs vibration analysis functions based on machine running speed to help diagnose faults such as unbalance, misalignment and looseness. The system is designed to enable you to take vibration measurements from assets like pumps, motors, fans and bearings. The unit displays vibration frequency plots and allows vibration severity and bearing condition to be monitored.

For documentation purpose, you can connect the XT280 to the XT Alignment App. Run the app on your phone or tablet*, or the XT Display unit.



Display on vibrometer unit. Live values.



Display on vibrometer unit. Analyze.



The XT280 connects to the XT Alignment App, making it possible to document the result as PDF, with photo and comments for each measurement point.

ACCESSORIES



Long probe, Part No. 03-1326



Magnet, Part No. 03-1327



Easy-Laser® XT280 VIB system, Part No. 12-1090		
1	Vibration meter	
1	USB memory stick with documentation	
1	Carrying case, WxHxD: 270x225x80 mm [10.6"x8.8"x3.1"]	

Vibration meter		
Frequency range	2 Hz to 1kHz (ISO) 1 kHz to 10 kHz (BDU)	
Max frequency resolution	1.25 Hz @ 800 lines FFT setting	
Displayed amplitude units	Acceleration in g	
	Velocity in mm/s (or inch/s)	
	Bearing noise in BDU (bearing damage units)	
Displayed Frequency Units	Hertz (Hz), RPM or CPM	
Input range	User selectable with accelerometer sensitivity	
Dynamic range	96 dB (0.01g resolution)	
VA diagnostic bands	Unbalance 1x RPM	
(RPM=run speed)	Alignment 2x RPM	
	Looseness 3x RPM	
Operating temperature	0°C to 50°C	
Storage temperature	-20°C to 70°C	
Battery type	2 x AA batteries	
Battery operation	20 hours continuously (depending on brightness setting)	
Environmental protection	IP67	
Material	ABS plastics / Hard anodized aluminium	
Dimensions	WxHxD: 200 mm x 60mm x 26mm [7.8 x 2.4 x 1.0"]	
Weight	280 g [9.8 oz]	

Download the free app!

Easy-Laser XT Alignment App





Hassellunden 11A, 2765 Smørum Tel. 45 95 04 10 info@buhl-bonsoe.dk www.buhl-bonsoe.dk















